

10901075 Cut Sheet



WERMA audible alarm buzzer, 80 dB at 1m, 2.1 kHz tone frequency, pulse tone(s), 24 VAC/VDC, 22mm, panel mount, ABS/polycarbonate housing, black, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10901075>

Technical Specifications

Brand	WERMA
Item	Audible alarm buzzer
Loudness Decibel	80 dB at 1m
Tone Frequency	2.1 kHz
Tone Type	Pulse
Touch to Acknowledge	No
Number of Alarms	1
Voltage Rating	24 VAC/VDC
Barrel Size	22mm
Mounting	Panel
Housing Material	ABS/polycarbonate
Color	Black
IP Rating	IP65

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/10901075.pdf>
See store item page for other formats.