

# 10901077 Cut Sheet



WERMA audible alarm buzzer, 80 dB at 1m, 2.1 kHz tone frequency, pulse tone(s), 115 VAC/VDC, 22mm, panel mount, ABS/polycarbonate housing, black, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10901077>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Audible alarm buzzer
<b>Loudness Decibel</b>	80 dB at 1m
<b>Tone Frequency</b>	2.1 kHz
<b>Tone Type</b>	Pulse
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	115 VAC/VDC
<b>Barrel Size</b>	22mm
<b>Mounting</b>	Panel
<b>Housing Material</b>	ABS/polycarbonate
<b>Color</b>	Black
<b>IP Rating</b>	IP65

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/10901077.pdf>  
See store item page for other formats.