

1097034 Cut Sheet



RUKO knockout punch, 3/4in conduit. Punch, die and draw bolt included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1097034>

Technical Specifications

Brand	RUKO
Item	Knockout punch
Replacement	No
Knockout Size	3/4in conduit
Hole Diameter	1-1/8in
Bolt Size	MF 12 x 1.5 x 60
Maximum Cutting Depth	5/32in (4mm)
Application	Hole cutting
For Use On	Steel, plastic, stainless steel and non-ferrous metals
Includes	Punch, die and draw bolt

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1097034.pdf>
See store item page for other formats.