

1099I220SBA Cut Sheet



KNIPEX hose clamp crimping tool, 8.8in (223mm) overall length, plastic coated handles, additional side jaw for easy clamping at 90deg and slim profile tool end.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1099I220SBA>

Technical Specifications

Brand	KNIPEX
Item	Hose clamp crimping tool
Overall Length	8.8in (223mm)
Insulated	No
Handle Type	Plastic coated handles
Application	Hose clamp crimping
Material	High-grade special tool steel, forged, oil-hardened
Tool Features	Additional side jaw for easy clamping at 90deg and slim profile tool end
Additional Information	For mounting 1-ear and 2-ear hose clamps

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement