

10MJ-8MB90 Cut Sheet



HY-TECH hydraulic fluid adapter, elbow, plated steel body, (1) -10 male JIC 37 deg and (1) -8 male o-ring boss. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10MJ-8MB90>

Technical Specifications

| | |
|-------------------|--------------------------------------------------------|
| Brand | HY-TECH |
| Item | Adapter |
| Working Fluid | Hydraulic fluid |
| Adapter Type | Elbow |
| Body Material | Plated steel |
| Thread Material | Plated steel |
| Measurement Type | SAE |
| Connection | (1) -10 male JIC 37 deg and (1) -8 male o-ring boss |
| Quantity per Pack | 2 |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |