

11000075 Cut Sheet



WERMA audible alarm buzzer, 100 dB at 1m, 1.6 kHz to 3.4 kHz tone frequency, (8) selectable tone(s), 24 VAC/VDC, 22mm, panel mount, ABS/polycarbonate housing, black, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/11000075>

Technical Specifications

Brand	WERMA
Item	Audible alarm buzzer
Loudness Decibel	100 dB at 1m
Tone Frequency	1.6 kHz to 3.4 kHz
Tone Type	(8) selectable
Touch to Acknowledge	No
Voltage Rating	24 VAC/VDC
Barrel Size	22mm
Mounting	Panel
Housing Material	ABS/polycarbonate
Color	Black
IP Rating	IP65

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document