

# 11005B Cut Sheet



Halex fitting, zinc die cast, 90-degree, 1/2in trade size, screw clamp conduit connection. Package of 25. For use with flexible metal conduit (FMC), AC cable (BX), MC cable. Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/11005B>

## Technical Specifications

<b>Brand</b>	Halex
<b>Item</b>	Fitting
<b>Liquid-tight</b>	No
<b>Fitting Type</b>	90-degree
<b>Material</b>	Zinc die cast
<b>Trade Size</b>	1/2in
<b>Conduit Connection Method</b>	Screw clamp
<b>Box Connection Type</b>	1/2in male NPSM
<b>Insulation</b>	No
<b>Knockout Size</b>	1/2in
<b>Reduced Wall Flexible Metal Conduit Trade Size</b>	1/2in

<b>Flexible Metal Conduit (FMC) Compatibility</b>	Aluminum FMC, aluminum RWFMFC, aluminum XRWFMC, steel FMC, steel RWFMFC and steel XRWFMC
<b>Armored Cable (AC) Size Range</b>	Aluminum 10/4-6/4 and steel 10/4-8/3
<b>Metal Clad (MC) Cable Size Range</b>	Aluminum 10/4-6/3 and steel 10/4-6/3
<b>Quantity per Pack</b>	25
<b>For Use With</b>	Flexible metal conduit (FMC), AC cable (BX), MC cable
<b>Includes</b>	Screws and locknut
<b>Applicable Standards</b>	UL 514B Listed

## Agency Approvals

<b>UL Listed File #</b>	E30248
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>