

11007B Cut Sheet



Hallex fitting, zinc die cast, 90-degree, 3/4in trade size, screw clamp conduit connection. Package of 10. For use with flexible metal conduit (FMC), AC cable (BX), MC cable. Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/11007B>

Technical Specifications

| | |
|---|-----------------|
| Brand | Hallex |
| Item | Fitting |
| Liquid-tight | No |
| Fitting Type | 90-degree |
| Material | Zinc die cast |
| Trade Size | 3/4in |
| Conduit Connection Method | Screw clamp |
| Box Connection Type | 3/4in male NPSM |
| Insulation | No |
| Knockout Size | 3/4in |
| Reduced Wall Flexible Metal Conduit Trade Size | 3/4in |

| | |
|---|---|
| Flexible Metal Conduit (FMC) Compatibility | Aluminum FMC, aluminum RWFMC, steel FMC, steel RWFMC and steel XRWFMC |
| Armored Cable (AC) Size Range | Aluminum 6/4-2/4 and steel 6/4-3/4 |
| Metal Clad (MC) Cable Size Range | Aluminum 8/4-3/4 and steel 8/4-3/4 |
| Quantity per Pack | 10 |
| For Use With | Flexible metal conduit (FMC), AC cable (BX), MC cable |
| Includes | Screws and locknut |
| Applicable Standards | UL 514B Listed |

Agency Approvals

| | |
|-------------------------|---|
| UL Listed File # | E30248 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |