

11015B Cut Sheet



Halex fitting, zinc die cast, 90-degree, 1-1/2in trade size, screw clamp conduit connection. Package of 5. For use with flexible metal conduit (FMC). Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/11015B>

Technical Specifications

Brand	Halex
Item	Fitting
Liquid-tight	No
Fitting Type	90-degree
Material	Zinc die cast
Trade Size	1-1/2in
Conduit Connection Method	Screw clamp
Box Connection Type	1-1/2in male NPSM
Insulation	No

Knockout Size	1-1/2in
Reduced Wall Flexible Metal Conduit Trade Size	1-1/2in
Flexible Metal Conduit (FMC) Compatibility	Aluminum FMC, aluminum RWFC, steel FMC and steel RWFC
Quantity per Pack	5
For Use With	Flexible metal conduit (FMC)
Includes	Screws and locknut
Applicable Standards	UL 514B Listed

Agency Approvals

UL Listed File #	E30248
CE	None
RoHS Status	No
EU REACH	View EU REACH document