

# 11035B Cut Sheet



Halex fitting, zinc die cast, 90-degree, 3-1/2in trade size, screw clamp conduit connection. Package of 1. For use with flexible metal conduit (FMC). Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/11035B>

## Technical Specifications

<b>Brand</b>	Halex
<b>Item</b>	Fitting
<b>Liquid-tight</b>	No
<b>Fitting Type</b>	90-degree
<b>Material</b>	Zinc die cast
<b>Trade Size</b>	3-1/2in
<b>Conduit Connection Method</b>	Screw clamp
<b>Box Connection Type</b>	3-1/2in male NPSM
<b>Insulation</b>	No

<b>Knockout Size</b>	3-1/2in
<b>Reduced Wall Flexible Metal Conduit Trade Size</b>	3-1/2in
<b>Flexible Metal Conduit (FMC) Compatibility</b>	Aluminum FMC, aluminum RWFC, steel FMC and steel RWFC
<b>Quantity per Pack</b>	1
<b>For Use With</b>	Flexible metal conduit (FMC)
<b>Includes</b>	Screws and locknut
<b>Applicable Standards</b>	UL 514B Listed

## Agency Approvals

<b>UL Listed File #</b>	E30248
<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>