

# 111000-01 Cut Sheet



Stego thermostat, adjustable, N.C. (open on rise) -10 to 50 deg C, 7K switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/111000-01>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Thermostat
<b>IP Rating</b>	IP20
<b>Setpoint Type</b>	Adjustable
<b>Contact 1</b>	N.C. (open on rise) -10 to 50 deg C
<b>Switching Differential</b>	7K
<b>Switching Tolerance</b>	+/-4K
<b>Maximum Switching Capacity</b>	15A resistive / 2A inductive at 120 VAC, 10A resistive / 2A inductive at 250 VAC, 30W DC
<b>Connection</b>	Push-in clamps for (2) AWG14 max stranded (with wire ferrule) or solid wire
<b>Mounting</b>	35mm DIN rail
<b>Application</b>	For electrical enclosure climate control

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E164102
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/111000-01.pdf>  
See store item page for other formats.