

# 111000-02 Cut Sheet



Stego thermostat, adjustable, N.C. (open on rise) 20 to 80 deg C, 7K switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/111000-02>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Thermostat
<b>IP Rating</b>	IP20
<b>Setpoint Type</b>	Adjustable
<b>Contact 1</b>	N.C. (open on rise) 20 to 80 deg C
<b>Switching Differential</b>	7K
<b>Switching Tolerance</b>	+/-4K
<b>Maximum Switching Capacity</b>	3A resistive / 2A inductive at 120 VAC, 3A resistive / 2A inductive at 250 VAC, 30W DC
<b>Connection</b>	Push-in clamps for (2) AWG14 max stranded (with wire ferrule) or solid wire
<b>Mounting</b>	35mm DIN rail
<b>Application</b>	For electrical enclosure climate control

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E164102
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>