

112430.00 Cut Sheet



Leeson Washguard White Duck standard efficiency AC induction motor, washdown and inverter rated, 3/4hp, 3-phase, 208-230/460 VAC, 1800rpm, TEFC, 56C frame, rolled steel, C-face/ rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/112430.00>

Technical Specifications

| | |
|--------------------------|-----------------------------|
| Brand | Leeson |
| Item | Motor |
| Series | Washguard White Duck |
| Efficiency Group | Standard efficiency |
| Efficiency | 77 |
| Voltage Type | AC |
| Motor Type | Induction |
| Motor Application | Washdown and inverter rated |
| Horsepower Rating | 3/4hp |
| Number of Phases | 3 |
| Voltage Rating | 208-230/460 VAC |
| Synchronous Speed | 1800rpm |
| Nameplate RPM | 1725rpm |
| Overload Type | None |
| Enclosure Type | TEFC |
| Shaft Type | Round with square key |

| | |
|---------------------------------|-----------------------------|
| Shaft Diameter | 5/8in |
| Shaft Material | 303 stainless (C-501) steel |
| Motor Frame | 56C |
| Frame Material | Rolled steel |
| Electrically Reversible | Yes |
| Insulation Class | Class F |
| IP Rating | IP55 |
| Constant Torque Rating | 10:1 |
| Variable Torque Rating | 10:1 |
| Service Factor | 1.15 |
| Integrated Brake | No |
| NEMA Design | Design B |
| Junction Box Orientation | F1 |
| Mounting | C-face/rigid base |
| Mounting Orientation | Horizontal or vertical |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E49747 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR2025 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/112430.00.pdf>
See store item page for other formats.