

# 1151E-6507 Cut Sheet



Eaton photoelectric sensor, rectangular, plastic housing, through-beam emitter, 500ft sensing distance, 10-40 VDC operating voltage, 4-wire, 4-pin mini connector and 7/8in - 16UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1151E-6507>

## Technical Specifications

<b>Brand</b>	Eaton
<b>Item</b>	Photoelectric sensor
<b>Shape</b>	Rectangular
<b>Housing Size</b>	73 x 48.5 x 46mm
<b>Thread mounting base size</b>	30mm
<b>IP Rating</b>	IP67
<b>Housing Material</b>	Plastic
<b>Sensing Method</b>	Through-beam emitter

<b>Operating Voltage</b>	10-40 VDC
<b>Number of Wires</b>	4
<b>Sensing Distance</b>	500ft
<b>Sensitivity</b>	Potentiometer
<b>Light Emission</b>	Infrared
<b>Connection</b>	4-pin mini connector and 7/8in - 16UNF thread
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>