

1151E-6513 Cut Sheet



Eaton photoelectric sensor, rectangular, plastic housing, through-beam emitter, infrared, 500ft sensing distance, 12-240 VDC/24-240 VAC operating voltage, 4-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1151E-6513>

Technical Specifications

Brand	Eaton	Number of Wires	4
Item	Photoelectric sensor	Sensing Distance	500ft
Shape	Rectangular	Sensitivity	Potentiometer
Housing Size	73 x 48.5 x 46mm	Light Emission (NP)	Infrared
Thread mounting base size	30mm	Cable Length	6ft/1.8m
IP Rating	IP67	Connection	Pigtail
Housing Material	Plastic	Conductor Size	20 AWG
Sensing Method	Through-beam emitter	Includes	Mounting hardware
Operating Voltage	12-240 VDC/24-240 VAC	Additional Information	Mounting nut included

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document