

1151E-6517 Cut Sheet



Eaton photoelectric sensor, rectangular, plastic housing, through-beam emitter, infrared light emission, 500ft sensing distance, 10-40 VDC operating voltage, 4-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1151E-6517>

Technical Specifications

Brand	Eaton
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	73 x 48.5 x 46mm
Thread mounting base size	30mm
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Through-beam emitter
Operating Voltage	10-40 VDC

Number of Wires	4
Sensing Distance	500ft
Sensitivity	Potentiometer
Light Emission	Infrared
Cable Length	6ft/1.8m
Connection	Pigtail
Conductor Size	20 AWG
Includes	Mounting hardware
Additional Information	Mounting nut included

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document