

1151E-6543 Cut Sheet



Eaton photoelectric sensor, rectangular, plastic housing, through-beam emitter, infrared, 500ft sensing distance, 12-240 VDC/24-240 VAC operating voltage, 4-wire, 4-pin AC micro connector and 1/2in - 20UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1151E-6543>

Technical Specifications

Brand	Eaton	Operating Voltage	12-240 VDC/24-240 VAC
Item	Photoelectric sensor	Number of Wires	4
Shape	Rectangular	Sensing Distance	500ft
Housing Size	73 x 48.5 x 46mm	Sensitivity	Potentiometer
Thread mounting base size	30mm	Light Emission (NP)	Infrared
IP Rating	IP67	Connection	4-pin AC micro connector and 1/2in - 20UNF thread
Housing Material	Plastic	Includes	Mounting hardware
Sensing Method	Through-beam emitter	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document