

118020-00 Cut Sheet



Stego Filter Fan grille, side mount, G3 (coarse) filter mat, NEMA 12, 6.93 x 6.93in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118020-00>

Technical Specifications

Brand	Stego
Series	Filter Fan
Item	Grille
Mounting	Side
With Air Flaps	No
Filter Media	G3 (coarse) filter mat
NEMA Rating	12
IP Rating	IP54 (IP55 with optional M5 filter media)
Enclosure Cutout	6.93 x 6.93in
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document