

# 118030-00 Cut Sheet



Stego Filter Fan grille, side mount, G3 (coarse) filter mat, NEMA 12, 9.84 x 9.84in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118030-00>

## Technical Specifications

|                         |   |
|-------------------------|---|
| <b>Brand</b>            | Stego                                     |
| <b>Series</b>           | Filter Fan                                |
| <b>Item</b>             | Grille                                    |
| <b>Mounting</b>         | Side                                      |
| <b>With Air Flaps</b>   | No  |
| <b>Filter Media</b>     | G3 (coarse) filter mat                    |
| <b>NEMA Rating</b>      | 12  |
| <b>IP Rating</b>        | IP54 (IP55 with optional M5 filter media) |
| <b>Enclosure Cutout</b> | 9.84 x 9.84in                             |
| <b>Color</b>            | RAL 7035 light gray                       |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E234324                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/118030-00.pdf>  
See store item page for other formats.