

# 118210-00 Cut Sheet



Stego Filter Fan grille, side mount, M5 (medium) filter mat, NEMA 12, 4.92 x 4.92in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118210-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Series</b>	Filter Fan
<b>Item</b>	Grille
<b>Mounting</b>	Side
<b>With Air Flaps</b>	No
<b>Filter Media</b>	M5 (medium) filter mat
<b>NEMA Rating</b>	12
<b>IP Rating</b>	IP55
<b>Enclosure Cutout</b>	4.92 x 4.92in
<b>Color</b>	RAL 7035 light gray

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/118210-00.pdf>  
See store item page for other formats.