

118210-00 Cut Sheet



Stego Filter Fan grille, side mount, M5 (medium) filter mat, NEMA 12, 4.92 x 4.92in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118210-00>

Technical Specifications

Brand	Stego
Series	Filter Fan
Item	Grille
Mounting	Side
With Air Flaps	No
Filter Media	M5 (medium) filter mat
NEMA Rating	12
IP Rating	IP55
Enclosure Cutout	4.92 x 4.92in
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document