

118700-00 Cut Sheet



Stego Filter Fan Plus FPI exhaust grille, side mount, with air flaps, NEMA 12, 3.62 x 3.62in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118700-00>

Technical Specifications

Brand	Stego
Series	Filter Fan Plus FPI
Airflow Direction	Exhaust
Item	Grille
Mounting	Side
With Air Flaps	Yes
NEMA Rating	12
IP Rating	IP54
Enclosure Cutout	3.62 x 3.62in
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document