

118710-00 Cut Sheet



Stego Filter Fan Plus FPI exhaust grille, side mount, with air flaps, NEMA 12, 4.88 x 4.88in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118710-00>

Technical Specifications

Brand	Stego
Series	Filter Fan Plus FPI
Airflow Direction	Exhaust
Item	Grille
Mounting	Side
With Air Flaps	Yes
NEMA Rating	12
IP Rating	IP54
Enclosure Cutout	4.88 x 4.88in
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/118710-00.pdf>
See store item page for other formats.