

118740-00 Cut Sheet



Stego Filter Fan Plus FPI exhaust grille, side mount, with air flaps, NEMA 12, 11.46 x 11.46in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/118740-00>

Technical Specifications

| | |
|--------------------------|---------------------|
| Brand | Stego |
| Series | Filter Fan Plus FPI |
| Airflow Direction | Exhaust |
| Item | Grille |
| Mounting | Side |
| With Air Flaps | Yes |
| NEMA Rating | 12 |
| IP Rating | IP54 |
| Enclosure Cutout | 11.46 x 11.46in |
| Color | RAL 7035 light gray |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/118740-00.pdf>
See store item page for other formats.