

121040-00 Cut Sheet



Stego Varioline LED enclosure light, 120 VAC operating voltage, on/off switch, 19.5in length, 1080 Lm, integral receptacle, screw mount, 3-pole plug with snap lock, 11W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/121040-00>

Technical Specifications

Brand	Stego
Item	LED enclosure light
Series	Varioline
Operating Voltage	120 VAC
Switch Type	On/off
Length	19.5in
Luminous Flux	1080 Lm
Integral Receptacle	Yes
Mounting	Screw
Connection	3-pole plug with snap lock
Power Consumption	11W
IP Rating	IP20
Requires	Power or extension cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document