

# 121240-00 Cut Sheet



Stego Varioline LED enclosure light, 120 VAC operating voltage, connection for external switch, 19.5in length, 1080 Lm, integral receptacle, screw mount, 3-pole plug with snap lock, 11W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/121240-00>

## Technical Specifications

|                            |                            |
|----------------------------|----------------------------|
| <b>Brand</b>               | Stego                      |
| <b>Item</b>                | LED enclosure light        |
| <b>Series</b>              | Varioline                  |
| <b>Operating Voltage</b>   | 120 VAC                    |
| <b>Switch Type</b>         | Connection for external    |
| <b>Length</b>              | 19.5in                     |
| <b>Luminous Flux</b>       | 1080 Lm                    |
| <b>Integral Receptacle</b> | Yes                        |
| <b>Mounting</b>            | Screw                      |
| <b>Connection</b>          | 3-pole plug with snap lock |
| <b>Power Consumption</b>   | 11W                        |
| <b>IP Rating</b>           | IP20                       |
| <b>Requires</b>            | Power or extension cable   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E234324                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |