

# 121240-30 Cut Sheet



Stego Varioline LED enclosure light, 120 VAC operating voltage, connection for external switch, 19.5in length, 1080 Lm, integral receptacle, magnet mount, 3-pole plug with snap lock, 11W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/121240-30>

## Technical Specifications

Brand	Stego
Item	LED enclosure light
Series	Varioline
Operating Voltage	120 VAC
Switch Type	Connection for external
Length	19.5in
Luminous Flux	1080 Lm
Integral Receptacle	Yes
Mounting	Magnet
Connection	3-pole plug with snap lock
Power Consumption	11W
IP Rating	IP20
Requires	M5 mounting screws and power or extension cable

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/121240-30.pdf>  
See store item page for other formats.