

# 121340-30 Cut Sheet



Stego Varioline LED enclosure light, 120 VAC operating voltage, no switch, 19.5in length, 1080 Lm, integral receptacle, magnet mount, 3-pole plug with snap lock, 11W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/121340-30>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	LED enclosure light
<b>Series</b>	Varioline
<b>Operating Voltage</b>	120 VAC
<b>Switch Type</b>	None
<b>Length</b>	19.5in
<b>Luminous Flux</b>	1080 Lm
<b>Integral Receptacle</b>	Yes
<b>Mounting</b>	Magnet
<b>Connection</b>	3-pole plug with snap lock
<b>Power Consumption</b>	11W
<b>IP Rating</b>	IP20
<b>Requires</b>	M5 mounting screws and power or extension cable

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/121340-30.pdf>  
See store item page for other formats.