

122MXL025NG Cut Sheet



SureMotion timing belt, 0.08in MXL pitch, 1/4in wide, 122 tooth, 9.8in pitch length (circumference), neoprene, fiberglass reinforced. Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/122MXL025NG>

Technical Specifications

Brand	SureMotion
Item	Timing belt
Pitch	0.08in MXL
Width	1/4in
Number of Teeth	122
Pitch length	9.8in
Material	Neoprene
Reinforcement	Fiberglass
Belt Tensile Rating	103lb
Quantity per Pack	3

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/122MXL025NG.pdf>
See store item page for other formats.