

126022 Cut Sheet



RUKO bi-metal hole saw, 7/8in (22mm), 8% cobalt high-speed steel (HSSE-Co8), hardened steel backer, fine tooth, 1.5in (38mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/126022>

Technical Specifications

Brand	RUKO
Item	Bi-metal hole saw
Hole Saw Size	7/8in (22mm)
Maximum Cutting Depth	1.5in (38mm)
Material	8% cobalt high-speed steel (HSSE-Co8)
Hardened Steel Backer	Yes
Tooth Density	6 teeth/in
Toothing	Fine tooth
Cutting Direction	Right hand
For Use On	Steel, stainless steel, aluminum, brass, plastic and bronze
Application	Hole cutting
Additional Information	Purchase arbor assembly separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document