

126304 Cut Sheet



RUKO bi-metal hole saw set, 13 pieces, 8% cobalt high-speed steel (HSSE-Co8), hardened steel backer, fine tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/126304>

Technical Specifications

Brand	RUKO
Item	Bi-metal hole saw set
Number of Pieces	13
Material	8% cobalt high-speed steel (HSSE-Co8)
Hole Saw Size	7/8in (22mm), 1in (25mm), 1-1/4in (32mm), 1-3/8in (35mm), 1-5/8in (41mm), 1-3/4in (44mm), 2in (51mm), 2-1/8in (54mm), 2-3/8in (60mm) and 2-1/2in (64mm)
Cutting Direction	Right hand
Hardened Steel Backer	Yes
Tooth Density	6 teeth/in
Toothing	Fine tooth
Set Includes	(10) hole saws (7/8, 1, 1-1/4, 1-3/8, 1-5/8, 1-3/4, 2, 2-1/8, 2-3/8 and 2-1/2in), (2) arbor assemblies (A2 and A4), 4mm Allen wrench, heavy-duty plastic case
Application	Hole cutting
For Use On	Steel, stainless steel, aluminum, brass, plastic and bronze

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document