

# 126304 Cut Sheet



RUKO bi-metal hole saw set, 13 pieces, 8% cobalt high-speed steel (HSSE-Co8), hardened steel backer, fine tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/126304>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Bi-metal hole saw set
<b>Number of Pieces</b>	13
<b>Material</b>	8% cobalt high-speed steel (HSSE-Co8)
<b>Hole Saw Size</b>	7/8in (22mm), 1in (25mm), 1-1/4in (32mm), 1-3/8in (35mm), 1-5/8in (41mm), 1-3/4in (44mm), 2in (51mm), 2-1/8in (54mm), 2-3/8in (60mm) and 2-1/2in (64mm)
<b>Cutting Direction</b>	Right hand

<b>Hardened Steel Backer</b>	Yes
<b>Tooth Density</b>	6 teeth/in
<b>Toothing</b>	Fine tooth
<b>Set Includes</b>	(10) hole saws (7/8, 1, 1-1/4, 1-3/8, 1-5/8, 1-3/4, 2, 2-1/8, 2-3/8 and 2-1/2in), (2) arbor assemblies (A2 and A4), 4mm Allen wrench, heavy-duty plastic case
<b>Application</b>	Hole cutting
<b>For Use On</b>	Steel, stainless steel, aluminum, brass, plastic and bronze

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>