

126318 Cut Sheet



RUKO bi-metal hole saw set, 20 pieces, 8% cobalt high-speed steel (HSSE-Co8), hardened steel backer, fine tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/126318>

Technical Specifications

Brand	RUKO
Item	Bi-metal hole saw set
Number of Pieces	20
Material	8% cobalt high-speed steel (HSSE-Co8)
Hole Saw Size	5/8in (16mm), 3/4in (19mm), 13/16in, 15/16in, 1in (25mm), 1-1/8in (29mm), 1-1/4in (32mm), 1-7/16in, 1-9/16in (40mm), 1-7/8in (48mm), 2in (51mm), 2-1/8in (54mm), 2-3/8in (60mm), 2-7/8in (73mm) and 3-1/4in (83mm)
Cutting Direction	Right hand
Hardened Steel Backer	Yes

Tooth Density	6 teeth/in
Toothing	Fine tooth
Set Includes	(15) hole saws (5/8, 3/4, 13/16, 15/16, 1, 1-1/8, 1-1/4, 1-7/16, 1-9/16, 1-7/8, 2, 2-1/8, 2-3/8, 2-7/8 and 3-1/4in), (2) arbor assemblies (A1 and A2), 1/4in pilot drill, 11.81in long extension, 4mm Allen wrench, heavy-duty plastic case
Application	Hole cutting
For Use On	Steel, stainless steel, aluminum, brass, plastic and bronze

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document