

# 126318 Cut Sheet



RUKO bi-metal hole saw set, 20 pieces, 8% cobalt high-speed steel (HSSE-Co8), hardened steel backer, fine tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/126318>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Bi-metal hole saw set
<b>Number of Pieces</b>	20
<b>Material</b>	8% cobalt high-speed steel (HSSE-Co8)
<b>Hole Saw Size</b>	5/8in (16mm), 3/4in (19mm), 13/16in, 15/16in, 1in (25mm), 1-1/8in (29mm), 1-1/4in (32mm), 1-7/16in, 1-9/16in (40mm), 1-7/8in (48mm), 2in (51mm), 2-1/8in (54mm), 2-3/8in (60mm), 2-7/8in (73mm) and 3-1/4in (83mm)
<b>Cutting Direction</b>	Right hand
<b>Hardened Steel Backer</b>	Yes
<b>Tooth Density</b>	6 teeth/in
<b>Toothing</b>	Fine tooth
<b>Set Includes</b>	(15) hole saws (5/8, 3/4, 13/16, 15/16, 1, 1-1/8, 1-1/4, 1-7/16, 1-9/16, 1-7/8, 2, 2-1/8, 2-3/8, 2-7/8 and 3-1/4in), (2) arbor assemblies (A1 and A2), 1/4in pilot drill, 11.81in long extension, 4mm Allen wrench, heavy-duty plastic case
<b>Application</b>	Hole cutting
<b>For Use On</b>	Steel, stainless steel, aluminum, brass, plastic and bronze

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>