

# 12MJ-8MB90 Cut Sheet



HY-TECH hydraulic fluid adapter, elbow, plated steel body, (1) -12 male JIC 37 deg and (1) -8 male o-ring boss. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/12MJ-8MB90>

## Technical Specifications

<b>Brand</b>	HY-TECH
<b>Item</b>	Adapter
<b>Working Fluid</b>	Hydraulic fluid
<b>Adapter Type</b>	Elbow
<b>Body Material</b>	Plated steel
<b>Thread Material</b>	Plated steel
<b>Measurement Type</b>	SAE
<b>Connection</b>	(1) -12 male JIC 37 deg and (1) -8 male o-ring boss
<b>Quantity per Pack</b>	2

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>