

130921-16 Cut Sheet



Stego enclosure heater, axial fan, 200W heating capacity, high performance cartridge heating element, 24 VDC operating voltage, adjustable thermostat, N.C. (open on rise) -4 to 104 deg F, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/130921-16>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	200W
Heating Element	High performance cartridge
Operating Voltage	24 VDC
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) -4 to 104 deg F
Switching Differential	5.4 deg F
Switching Tolerance	+/-1.8 deg F
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/130921-16.pdf>
See store item page for other formats.