

130921-17 Cut Sheet



Stego enclosure heater, axial fan, 200W heating capacity, high performance cartridge heating element, 24 VDC operating voltage, adjustable thermostat with external sensor connection, N.C. (open on rise) -4 to 104 deg F, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/130921-17>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	200W
Heating Element	High performance cartridge
Operating Voltage	24 VDC
Heater Control	Adjustable thermostat with external sensor connection
Contact 1	N.C. (open on rise) -4 to 104 deg F
Switching Differential	5.4 deg F
Switching Tolerance	+/-1.8 deg F
Mounting	35mm DIN rail or panel
Requires	External temperature sensor

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/130921-17.pdf>
See store item page for other formats.