

# 13256662055 Cut Sheet



Pfannenberg DTT 6601 air conditioner, 10000 BTU/H, R-134a, 460 VAC operating voltage, carbon steel housing, RAL 7035 light gray, filter-free, top mount. For use with NEMA/UL Type 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/13256662055>

## Technical Specifications

Brand	Pfannenberg
Series	DTT 6601
Item	Air conditioner
Nominal Cooling Capacity	10000 BTU/H
Operating Voltage	460 VAC
Frequency	50/60 Hz
Running Current	4.5A
Refrigerant	R-134a
Height	19.1in
Width	31.3in
Depth	22.64in

Mounting	Top
Filter-Free	Yes
Housing Material	Carbon steel
Color	RAL 7035 light gray
IP Rating	IP54
For Use With	NEMA/UL Type 12 enclosures
Includes	Seal, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none"><li>• Packaging Instructions: 200</li><li>• UN Number: 3159</li><li>• Hazard Type: Compressed Gas</li></ul>

## Agency Approvals

UL Listed File #	SA10300
UL Recognized File #	SA10300
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/13256662055.pdf>  
See store item page for other formats.