

# 13384136158 Cut Sheet



Pfannenberg DTS 3481C air conditioner, 20000 BTU/H, R-134a, 460 VAC operating voltage, 304 stainless steel housing, filter-free, side mount. For use with NEMA/UL Type 4 & 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/13384136158>

## Technical Specifications

Brand	Pfannenberg
Series	DTS 3481C
Item	Air conditioner
Nominal Cooling Capacity	20000 BTU/H
Operating Voltage	460 VAC
Frequency	50/60 Hz
Running Current	4.06A
Refrigerant	R-134a
Height	57.2in
Width	15.8in

Depth	16.1in
Mounting	Side
Filter-Free	Yes
Housing Material	304 stainless steel
IP Rating	IP56
For Use With	NEMA/UL Type 4 & 4X enclosures
Includes	Seal, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none"><li>• Packaging Instructions: 200</li><li>• UN Number: 3159</li><li>• Hazard Type: Compressed Gas</li></ul>

## Agency Approvals

UL Listed File #	SA10300
UL Recognized File #	SA10300
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/13384136158.pdf>  
See store item page for other formats.