

13384136355 Cut Sheet



Pfannenberg DTS 3461C air conditioner, 20000 BTU/H, R-134a, 460 VAC operating voltage, carbon steel housing, RAL 7035 light gray, filter-free, side mount. For use with NEMA/UL Type 3R & 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/13384136355>

Technical Specifications

Brand	Pfannenberg
Series	DTS 3461C
Item	Air conditioner
Nominal Cooling Capacity	20000 BTU/H
Operating Voltage	460 VAC
Frequency	50/60 Hz
Running Current	4.06A
Refrigerant	R-134a
Height	57.2in
Width	15.8in
Depth	16.1in

Mounting	Side
Filter-Free	Yes
Housing Material	Carbon steel
Color	RAL 7035 light gray
IP Rating	IP56
For Use With	NEMA/UL Type 3R & 4 enclosures
Includes	Seal, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA10300
UL Recognized File #	SA10300
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/13384136355.pdf>
See store item page for other formats.