

# 13385444158 Cut Sheet



Pfannenberg DTS 3181 air conditioner, 4100 BTU/H, R-134a, 115 VAC operating voltage, 304 stainless steel housing, filter-free, side mount. For use with NEMA/UL Type 4 & 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/13385444158>

## Technical Specifications

Brand	Pfannenberg
Series	DTS 3181
Item	Air conditioner
Nominal Cooling Capacity	4100 BTU/H
Operating Voltage	115 VAC
Frequency	60 Hz
Running Current	7.51A
Refrigerant	R-134a
Height	29.46in
Width	15.55in

Depth	9.3in
Mounting	Side
Filter-Free	Yes
Housing Material	304 stainless steel
IP Rating	IP56
For Use With	NEMA/UL Type 4 & 4X enclosures
Includes	Seal, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none"><li>• Packaging Instructions: 200</li><li>• UN Number: 3159</li><li>• Hazard Type: Compressed Gas</li></ul>

## Agency Approvals

UL Listed File #	SA10300
UL Recognized File #	SA10300
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/13385444158.pdf>  
See store item page for other formats.