

1351E-6547 Cut Sheet



Eaton photoelectric sensor, rectangular, diffuse, infrared light emission, 10ft sensing distance, selectable light-on/dark-on, NPN/PNP, potentiometer, 500 Hz switching frequency, plastic housing, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1351E-6547>

Technical Specifications

Brand	Eaton
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	73 x 48.5 x 46mm
Thread mounting base size	30mm
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Diffuse
Operating Voltage	10-40 VDC
Number of Wires	4

Switching Output	NPN/PNP
Sensing Distance	10ft
Sensitivity	Potentiometer
Operation Mode	Selectable light-on/dark-on
Switching Frequency	500 Hz
Light Emission	Infrared
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document