

14060S Cut Sheet



Southwire TechnicianPRO autoranging digital multimeter, AC/DC voltage, AC/DC current, resistance, continuity, capacitance, frequency and temperature, CAT IV 600V/CAT III 1000V. Test leads included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/14060S>

Technical Specifications

Brand	Southwire
Item	Multimeter
Series	TechnicianPRO
Safety Rating	CAT IV 600V/CAT III 1000V
AC Voltage Range	0-6.000 VAC, 0-60.00 VAC, 0-600.0 VAC and 0-1000 VAC
DC Voltage Range	0-600.0mVDC, 0-6.000 VDC, 0-60.00 VDC, 600.0 VDC and 0-1000 VDC
AC Current Range	0-600.0 μ A, 0-6000 μ A, 0-60.00 mA, 0-600.0 mA and 0-10.00A
DC Current Range	0-600.0 μ A, 0-6000 μ A, 0-60.00 mA, 0-600.0 mA and 0-10.00A
Resistance Range	0-600.0 ohm, 0-6.000 kohm, 0-60.00 kohm, 0-600.0 kohm, 0-6.000 Mohm and 0-60.00 Mohm
Capacitance Range	0-40.00 nF, 0-400.0 nF, 0-4.000 μ F, 0-40.00 μ F, 0-400.0 μ F and 0-4000 μ F
Frequency Range	0-9.999 Hz, 0-99.99 Hz, 0-999.9 Hz and 0-9.999 kHz
Temperature Range	-4 degrees F to 1400 degrees F and -20 degrees C to 780 degrees C
Continuity	<30 ohm
Includes	Test leads
Application	Electrical testing and continuity testing

Agency Approvals

UL Listed File #	E361819
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	No
EU REACH	View EU REACH document