

# 1414N4PHS16M8 Cut Sheet



Hammond enclosure, NEMA 3R/4/4X/12/13, 14 x 12 x 8in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, single-door, stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1414N4PHS16M8>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Hammond               |
| <b>Item</b>                         | Enclosure             |
| <b>Subpanel</b>                     | Subpanel included     |
| <b>Slope Top</b>                    | No                    |
| <b>3-Piece Assembly</b>             | No                    |
| <b>Vented</b>                       | No                    |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13         |
| <b>IP Rating</b>                    | IP66                  |
| <b>Nominal Enclosure Dimensions</b> | 14 x 12 x 8in (HxWxD) |
| <b>Enclosure Height</b>             | 14.31in               |
| <b>Enclosure Width</b>              | 12.31in               |
| <b>Enclosure Depth</b>              | 8.20in                |
| <b>Mounting</b>                     | Wall                  |
| <b>Integral Mounting Feet</b>       | Yes                   |

|                                  |                        |
|----------------------------------|------------------------|
| <b>Integral Mounting Flange</b>  | No                     |
| <b>Dual Access</b>               | No                     |
| <b>Knockouts</b>                 | No                     |
| <b>Bottom Gland Plate</b>        | No                     |
| <b>Material</b>                  | 316 stainless steel    |
| <b>Finish</b>                    | #4 brush               |
| <b>Cover Type</b>                | Single-door            |
| <b>Hinge Type</b>                | Continuous hinge       |
| <b>Number of Hinges Per Door</b> | 1                      |
| <b>Latch Type</b>                | Stainless steel clamps |
| <b>Number Of Latches</b>         | 2                      |
| <b>Shelf</b>                     | No                     |
| <b>Padlockable</b>               | No                     |
| <b>Keylocking</b>                | No                     |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1414N4PHS16M8.pdf>  
See store item page for other formats.