

# 1418JL7 Cut Sheet



Hammond enclosure, NEMA 12, 36 x 24 x 7in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1418JL7>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Hammond               |
| <b>Item</b>                         | Enclosure             |
| <b>Subpanel</b>                     | Subpanel included     |
| <b>Slope Top</b>                    | No                    |
| <b>3-Piece Assembly</b>             | No                    |
| <b>Vented</b>                       | No                    |
| <b>NEMA Rating</b>                  | 12                    |
| <b>IP Rating</b>                    | IP54                  |
| <b>Nominal Enclosure Dimensions</b> | 36 x 24 x 7in (HxWxD) |
| <b>Enclosure Height</b>             | 36.31in               |
| <b>Enclosure Width</b>              | 24.38in               |
| <b>Enclosure Depth</b>              | 7.17in                |
| <b>Mounting</b>                     | Wall                  |
| <b>Integral Mounting Feet</b>       | Yes                   |

|                                  |                    |
|----------------------------------|--------------------|
| <b>Integral Mounting Flange</b>  | No                 |
| <b>Dual Access</b>               | No                 |
| <b>Knockouts</b>                 | No                 |
| <b>Bottom Gland Plate</b>        | No                 |
| <b>Material</b>                  | Carbon steel       |
| <b>Color</b>                     | ANSI 61 gray       |
| <b>Finish</b>                    | Powder coat        |
| <b>Cover Type</b>                | Hinged screw cover |
| <b>Hinge Type</b>                | Continuous hinge   |
| <b>Number of Hinges Per Door</b> | 1                  |
| <b>Shelf</b>                     | No                 |
| <b>Padlockable</b>               | No                 |
| <b>Keylocking</b>                | No                 |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1418JL7.pdf>  
See store item page for other formats.