

# 1418N4S16S10 Cut Sheet



Hammond enclosure, NEMA 3R/4/4X/12/13, 48 x 36 x 10in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, single-door, stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1418N4S16S10>

## Technical Specifications

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Brand</b>                        | Hammond                |
| <b>Item</b>                         | Enclosure              |
| <b>Subpanel</b>                     | Subpanel included      |
| <b>Slope Top</b>                    | No                     |
| <b>3-Piece Assembly</b>             | No                     |
| <b>Vented</b>                       | No                     |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13          |
| <b>IP Rating</b>                    | IP66                   |
| <b>Nominal Enclosure Dimensions</b> | 48 x 36 x 10in (HxWxD) |
| <b>Enclosure Height</b>             | 48.00in                |
| <b>Enclosure Width</b>              | 36.00in                |
| <b>Enclosure Depth</b>              | 11.20in                |
| <b>Mounting</b>                     | Wall                   |
| <b>Integral Mounting Feet</b>       | Yes                    |
| <b>Integral Mounting Flange</b>     | No                     |

|                                  |                         |
|----------------------------------|-------------------------|
| <b>Dual Access</b>               | No                      |
| <b>Knockouts</b>                 | No                      |
| <b>Bottom Gland Plate</b>        | No                      |
| <b>Material</b>                  | 316 stainless steel     |
| <b>Finish</b>                    | #4 brush                |
| <b>Cover Type</b>                | Single-door             |
| <b>Hinge Type</b>                | Continuous hinge        |
| <b>Number of Hinges Per Door</b> | 1                       |
| <b>Latch Type</b>                | Stainless steel clamps  |
| <b>Number Of Latches</b>         | 8                       |
| <b>Padlock Attachment Type</b>   | Padlock hasp and staple |
| <b>Shelf</b>                     | No                      |
| <b>Padlockable</b>               | Yes                     |
| <b>Keylocking</b>                | No                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1418N4S16S10.pdf>  
See store item page for other formats.