

1418N4SSJ8 Cut Sheet



Hammond enclosure, NEMA 3R/4/4X/12/13, 24 x 24 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1418N4SSJ8>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Hammond |
| Item | Enclosure |
| Subpanel | Subpanel included |
| Slope Top | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 24 x 24 x 8in (HxWxD) |
| Enclosure Height | 24.00in |
| Enclosure Width | 24.00in |
| Enclosure Depth | 9.20in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |

| | |
|----------------------------------|-------------------------|
| Dual Access | No |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | Stainless steel clamps |
| Number Of Latches | 4 |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |