

1422N4B10F Cut Sheet



Hammond enclosure, NEMA 3R/4/12/13, 60 x 48 x 10in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1422N4B10F>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	60 x 48 x 10in (HxWxD)
Enclosure Height	60.13in
Enclosure Width	48.06in
Enclosure Depth	11.88in
Mounting	Floor
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	Stainless steel clamps
Number Of Latches	6
Padlock Attachment Type	Padlock hasp and staple
Shelf	No
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1422N4B10F.pdf>
See store item page for other formats.