1422N4B10F Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Hammond enclosure, NEMA 3R/4/12/13, 60 x 48 x 10in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/1422N4B10F

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Nominal Enclosure Height	60in
Nominal Enclosure Width	48in
Nominal Enclosure Depth	10in
Mounting	Floor
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No

Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	Stainless steel clamps
Number Of Latches	6
Padlock Attachment Type	Padlock hasp and staple
Shelf	No
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/1422N4B10F.pdf
See store item page for other formats.