

1435MS16C Cut Sheet



Hammond pushbutton enclosure, 3 holes, 22mm, NEMA 3R/4/4X, 8 x 4 x 3in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1435MS16C>

Technical Specifications

Brand	Hammond
Item	Pushbutton enclosure
Number of Pushbutton Holes	3 holes
Pushbutton Hole Nominal Size	22mm
Slope Top	No
NEMA Rating	3R/4/4X
IP Rating	IP66
Nominal Enclosure Dimensions	8 x 4 x 3in (HxWxD)
Enclosure Height	8.31in
Enclosure Width	3.56in

Enclosure Depth	2.92in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	316 stainless steel
Finish	#4 brush
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1435MS16C.pdf>
See store item page for other formats.